

Two Hole Cable Strap



CERTIFICATIONS



FEATURES

Secures lightning protection conductors and prevents displacement

Mechanically secured with screws or nails

SPECIFICATIONS

Table 1/2


Catalog Number	Material	Finish	Outer Diameter (OD)	Depth (D)	Height (H)	Width (W)
LPA804	Aluminum		12 mm	12.7mm	11.18 mm	41.91 mm
LPC802	Copper		12 mm	9.84mm	11.18 mm	41.91 mm
LPC804	Copper		12 mm	12.7mm	11.18 mm	41.91 mm
LPA808	Aluminum		33 mm	31.75mm	35.05 mm	109.47 mm

CatalogNumber	Material	Finish	Outer Diameter (OD)	Depth (D)	Height (H)	Width (W)
LPC808	Copper		33 mm	31.75mm	34.31 mm	109.47 mm
LPC808L	Copper	Tinned	33 mm	31.75mm	34.31 mm	109.47 mm
LPC806	Copper		12.7 mm	15.88mm	11.94 mm	53.6 mm

Table 2/2

Catalog Number	Hole Size (HS)	Certifications
LPA804	4.76 mm	
LPC802	4.76 mm	E202878-Combined_CoC, E202878-Combined_CoC
LPC804	4.76 mm	E202878-Combined_CoC, E202878-Combined_CoC
LPA808	7.14 mm	
LPC808	7.14 mm	E202878-Combined_CoC, E202878-Combined_CoC
LPC808L	7.14 mm	E202878-Combined_CoC, E202878-Combined_CoC
LPC806	7.14 mm	E202878-Combined_CoC, E202878-Combined_CoC

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE