

CABS Aluminum Profile, UL®



CERTIFICATIONS







FEATURES

For use with CABS module kits, UL

Available in multiple lengths to accommodate various widths and depths of enclosures

Factory punched holes for quick assembly

Evenly spaced holes provide consistent and accurate spacing

Improve bending resistance by interlocking or stacking two profiles

Time-savings and lower total install costs compared to traditional methods

Engineered and standardized design

RoHS compliant

SPECIFICATIONS


Material: AluminumFinish: Anodized

			Table 1/2			
Catalog Number	Article Number	Length (L)	Height (H)	Width (W)	Hole Size (HS)	A

CABSAL18	549512	457.2mm	29.2 mm	45.7 mm	11.9 mm	19 mm
CABSAL36	549515	914.4mm	29.2 mm	45.7 mm	11.9 mm	19 mm
CABSAL54	549517	1371.6mm	29.2 mm	45.7 mm	11.9 mm	19 mm
CABSAL24	549513	609.6mm	29.2 mm	45.7 mm	11.9 mm	19 mm
CABSAL48	549516	1219.2mm	29.2 mm	45.7 mm	11.9 mm	19 mm
CABSAL30	549514	762mm	29.2 mm	45.7 mm	11.9 mm	19 mm

Table 2/2						
Catalog Number	Article Number	Unit Weight				
CABSAL18	549512	0.69 kg				
CABSAL36	549515	1.38 kg				
CABSAL54	549517	2.07 kg				
CABSAL24	549513	0.92 kg				
CABSAL48	549516	1.84 kg				
CABSAL30	549514	1.15 kg				

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE