

APO Non-Metallic Mounting Feet

APO Mounting Feet allows APO enclosure mounting to any vertical surface supporting the load of the enclosure.



FEATURES

Set of four pieces

For heavy duty mounting

The brackets are mounted directly to the rear of the box in provided reinforcements

M4 threaded inserts are provided for secure attachment

Maximum load cannot exceed 330lbs (150kg)

SPECIFICATIONS

| Table 1/1 | | | | | |
|----------------|----------------|-----------------|--------------|-------|------------|
| Catalog Number | Article Number | Material | Finish | Color | Quick Ship |
| 41525.050 | 41525.050 | Polyamide | Smooth Matte | Black | No |
| AP-MFSS | AP-MFSS | Stainless Steel | Mill | | No |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE