

## Compact Series 2 Swivel Tilt 90-Degree Elbow



Compact Series 2 Swivel Tilt 90-Degree Elbow mounts between a horizontal tube and the enclosure to provide both swivel and tilt options for the machine operator. A 90-degree elbow is incorporated into this design for connecting to a horizontal tube. Swivel allows 300-degree maximum rotation. Tilt allows infinite adjustment from horizontal to 30 degrees. Maximum load is 66 lb. (30 kg).

### FEATURES

---

Coupling can rotate 300 degrees and tilt from horizontal to 30-degree

Installation hardware, mounting fasteners and gasket included

Assembled Compact Series 2 HMI Arm System has a max weight load of 101 lb. (45.8 kg)

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Material	Finish	Color
CCS2ESTLG	41899	45mm	60mm	Aluminum	Powder Coated	Light Gray

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE