

Elbow 90-Degree Outside Opening Lay-in Galvanized



Lay-in Galvanized 90-Degree Elbows with Outside Opening are used for continuous run with 90-degree turns. Top, bottom and outside covers removable. Lay-in feature allows wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system.

FEATURES

Lay-in Galvanized 90-Degree Elbows with Outside Opening are used for continuous run with 90-degree turns

Top, bottom and outside covers removable

Lay-in feature allows wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

SPECIFICATIONS

Finish: Galvanized

Material: Mild Steel

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
F8890EOUTGV	13162	Elbow	203mm	203mm	1.9mm	No
F121290EOUTGV	13164	Elbow	305mm	305mm	1.9mm	No
F4490EOUTGV	13158	Elbow	102mm	102mm	1.52mm	No
F6690EOUTGV	13161	Elbow	152mm	152mm	1.52mm	No
F101090EOUTGV	13163	Elbow	254mm	254mm	1.9mm	No
F2290EOUTGV	13157	Elbow	64mm	64mm	1.52mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE