

Hinged Cover Wiring Trough NEMA Type 12, 6.00x6.00x18.00, Gray, Steel

CATALOG NUMBER

F66T18HC



Hinged-Cover Wiring Trough, Type 12 is used for protecting wire and cable distribution, junctions and terminations in a variety of applications. This wiring trough meets basic functionality requirements for moist or dirty applications, with the added feature of a hinged, screw clamp cover for easy access.

INDUSTRY STANDARDS

UL 870 Listed; File No. E27524

NEMA Type 12

JIC standards EGP-1-1967 and EMP-1-1967

CSA, File No. 42184, Type 1

IEC 60529, IP55

FEATURES

Ends and seams continuously welded and ground smooth

No holes or knockouts

Butt hinges

External screw clamps

Oil-resistant gasket and adhesive

PRODUCT ATTRIBUTES

Article Number: 16670

Type: Trough

Height: 152mm

Width: 152mm

Depth: 457mm

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 1.9mm

Clamp Quantity: 2

Mounting Bracket Quantity: 2

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE