

Fixed Shelf



Fixed Shelves mount to the front and back rack angles. The shelf is adjustable with 12 gauge steel supports. Adjustable to fit multiple-depth enclosures or rack angle placements. Load rating is 150 lb. (68 kg). Rack accessories that are shorter than the enclosure depth can be mounted to rack angles or frame accessory brackets attached to grid straps. Order these items separately.

SPECIFICATIONS

Thickness: 1.9mm
Color: Light Gray
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Material	Quick Ship
P19SH5	71960	Mild Steel	No
P19SH6	71970	Mild Steel	No
P19SH8	71990	Mild Steel	No
P19SH9	72370	Mild Steel	No
P23SH5	72390	Mild Steel	No
P23SH6	72630	Mild Steel	No
P23SH8	72960	Mild Steel	No
P24SH5	72990	Mild Steel	No
P24SH6	73540	Mild Steel	No
P24SH8	73560	Mild Steel	No
P24SH9	73570	Mild Steel	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE