

ProLine G2 Perforated Door



ProLine G2 Perforated Doors (Single or Overlapping Double) can be used on the front or rear of a G2 enclosure to provide ventilation for cooling internal components. The Smooth Glide latching system is made from quality components and incorporates an innovative timed latch action ensuring a solid door seal with low closure force.

FEATURES

Smooth Glide latching system – for a smooth, reliable and repeatable door close over enclosure lifetime

Flush Swing Handle with key lock; other options available

Seamless Polyurethane gasket (UL Component Recognized) provides a water-tight, dust-tight seal against moisture and contaminants that could enter at the frame/door junction

Standard door bar system on all perforated doors for easy accessory attachment

Timed, 3-point latch engagement to ensure top and bottom of door catch reliably

Durable, double-flanged latch rod and three Delrin® rollers to prevent metal-on-metal grinding

Single doors can be hinged left or right (default left); overlapping double doors can have the primary door as the left or right (default right)

140-degree hinging standard (180-degree hinge option available)

Two grounding studs

All mounting hardware included

Overlapping Double Doors – Additional Specifications: Primary door with Smooth Glide latching system; secondary door has two latch points with a center lever to ensure secure door closure

SPECIFICATIONS

Thickness: 1.9mm
Color: Light Gray
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

| Catalog Number | Article Number | Material | Door Type | Quick Ship |
|----------------|----------------|------------|--------------------|------------|
| P2DP186 | 36137 | Mild Steel | Single Door | No |
| P2DP188 | 36138 | Mild Steel | Single Door | No |
| P2DP206 | 36141 | Mild Steel | Single Door | No |
| P2DP208 | 36142 | Mild Steel | Single Door | No |
| P2DP226 | 36143 | Mild Steel | Single Door | No |
| P2DP228 | 36144 | Mild Steel | Single Door | No |
| P2DP01812 | 36145 | Mild Steel | Overlapping Double | No |
| P2DP02012 | 36146 | Mild Steel | Overlapping Double | No |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE