

RackPower Basic PDU, RB0xxx, 120/208 VAC, 3-phase

Power Utilities

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 / C19 Combo outlets.

FEATURES

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 100-120/200-240VAC, 3-phase WYE

Connecting cable 6", with NEMA L21 connector

C13 and C13/C19 Combo outlets

1RU aluminum profile

Adjustable Toolless Mounting

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Socket Type	Color	Length	Voltage AC	Depth
RB0851	Socket Strip	IEC C13, IEC C13/C19	Black	1780 mm	208 V	55 mm

Table 2/2

Catalog Number	Width
RB0851	56 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE