

On Demand Stock Panels: NGC-30



nVent RAYCHEM NGC-30 On Demand Stock Panels offer rapid delivery of optimized best-in-class standard panel configurations for customer projects. Panels are built with quality components including premium RAYCHEM controllers for use in hazardous and nonhazardous areas. Many configurations have C1D2 circuit breakers and Type 4X stainless steel enclosures.

FEATURES

Improve efficiency and reduce lead times by using standardized EHT controller & panel designs

Broad selection of configurations available immediately with best-in-class advanced control options

Consistent design with time-tested quality for your project

SPECIFICATIONS

Table 1/1					
Catalog Number	Main Circuit Breaker Current Rating	Touchscreen Included	Circuit Breaker Voltage Rating	Control Relay Type	Voltage Rating
10721-024	80 A	Yes	277 V	Solid State	277 – 480 V
10721-026	225 A	Yes	120 V	Electromechanical	120 – 208 V
10721-022	175 A	Yes	277 V	Solid State	277 – 480 V
10721-023	125 A	Yes	277 V	Solid State	277 – 480 V
10721-025	225 A	Yes	120 V	Electromechanical	120 – 208 V

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com Europe, Middle East, Africa

Tel +32.16.213.511 Fax +32.16.213.604 thermal.info@nvent.com **Asia Pacific**

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com **Latin America**

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com