


EuropacPRO Advanced EMC Side Panel Cover

Aluminium Side panel 3mm to increase the EMC shielding effect of the subrack by covering the not needed cut-outs.



CERTIFICATIONS



FEATURES

Side panel covers for increased lateral RF shielding

Assembled on the outside of the standard side panel

Assembly material included

SPECIFICATIONS

Material:	Aluminum
Product Family:	EuropacPRO
Finish:	Passivated
Product Type:	Side Panel
Works With:	Sub racks
Type:	Type H
EMC Shielding:	Yes

Table 1/1

Catalog Number	Rack Height	Depth	Package Quantity	Length	Package Unit	Quick Ship
24563-255	3U	175mm	2	175mm	Pair	No
24563-256	3U	235mm	2	235mm	Pair	No

CatalogNumber	Rack Height	Depth	Package Quantity	Length	Package Unit	Quick Ship
24563-257	3U	275mm	2	275mm	Pair	No
24563-275	6U	175mm	2	175mm	Pair	No
24563-260	3U	355mm	2	355mm	Pair	No
24563-276	6U	235mm	2	235mm	Pair	No
24563-268	4U	355mm	2	355mm	Pair	No
24563-277	6U	275mm	2	275mm	Pair	No
24563-258	3U	277.75mm	2	277.75mm	Pair	No
24563-259	3U	295mm	2	295mm	Pair	No
24563-261	3U	415mm	2	415mm	Pair	No
24563-262	3U	495mm	2	495mm	Pair	No
24563-265	4U	175mm	2	175mm	Pair	No
24563-266	4U	235mm	2	235mm	Pair	No
24563-267	4U	295mm	2	295mm	Pair	No
24563-269	4U	415mm	2	415mm	Pair	No
24563-270	4U	495mm	2	495mm	Pair	No
24563-278	6U	277.75mm	2	277.75mm	Pair	No
24563-279	6U	295mm	2	295mm	Pair	No
24563-280	6U	355mm	2	355mm	Pair	No

CatalogNumber	Rack Height	Depth	Package Quantity	Length	Package Unit	Quick Ship
24563-281	6U	415mm	2	415mm	Pair	No
24563-282	6U	495mm	2	495mm	Pair	No

ADDITIONAL PRODUCT DETAILS

Side panel and 19" bracket are tox-cold welded together. toxen = Clinching technique, without add aids. This takes place with special tools and high pressure.

9 U version available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE