

# Plug-In Unit Kit With Trapezoid Handle, Shielded, Grey



Plug-in unit, with static handle and U-shaped front panel. The grey handle is assembled on the front panel. The U-shaped panel enables the assembly of a textile gasket.

## CERTIFICATIONS



## FEATURES

Front panel, U-profile, shielded

Handle without extraction function

## SPECIFICATIONS

|                       |                               |
|-----------------------|-------------------------------|
| <b>Material:</b>      | Aluminum                      |
| <b>Finish:</b>        | Anodized; Passivated          |
| <b>Product Type:</b>  | Front Panel                   |
| <b>Type:</b>          | Front Panel with Handle (PIU) |
| <b>EMC Shielding:</b> | Yes                           |

Table 1/3

| Catalog Number | Rack Height | Rack Width | Package Quantity | Handle Type       | Mounting       | Gasket Type |
|----------------|-------------|------------|------------------|-------------------|----------------|-------------|
| 20848-663      | 3U          | 3HP        | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |

| CatalogNumber | Rack Height | Rack Width | Package Quantity | Handle Type       | Mounting       | Gasket Type |
|---------------|-------------|------------|------------------|-------------------|----------------|-------------|
| 20848-664     | 3U          | 4HP        | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-665     | 3U          | 5HP        | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-666     | 3U          | 6HP        | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-667     | 3U          | 7HP        | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-668     | 3U          | 8HP        | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-669     | 3U          | 10HP       | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-671     | 6U          | 3HP        | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-670     | 3U          | 12HP       | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-672     | 6U          | 4HP        | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-675     | 6U          | 7HP        | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-673     | 6U          | 5HP        | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-674     | 6U          | 6HP        | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-676     | 6U          | 8HP        | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-677     | 6U          | 10HP       | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |
| 20848-678     | 6U          | 12HP       | 1                | Trapezoid, Static | Screw-on Front | Textile EMC |

Table 2/3

| Catalog Number | Front Finish | Rear Finish | Treated Edges | Flammability Rating | Complies With                             | Height (H) |
|----------------|--------------|-------------|---------------|---------------------|-------------------------------------------|------------|
| 20848-663      | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 128.4mm    |

| CatalogNumber | Front Finish | Rear Finish | Treated Edges | Flammability Rating | Complies With                             | Height (H) |
|---------------|--------------|-------------|---------------|---------------------|-------------------------------------------|------------|
| 20848-664     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 128.4mm    |
| 20848-665     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 128.4mm    |
| 20848-666     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 128.4mm    |
| 20848-667     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 128.4mm    |
| 20848-668     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 128.4mm    |
| 20848-669     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 128.4mm    |
| 20848-671     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 261.8mm    |
| 20848-670     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 128.4mm    |
| 20848-672     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 261.8mm    |
| 20848-675     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 261.8mm    |
| 20848-673     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 261.8mm    |

| CatalogNumber | Front Finish | Rear Finish | Treated Edges | Flammability Rating | Complies With                             | Height (H) |
|---------------|--------------|-------------|---------------|---------------------|-------------------------------------------|------------|
| 20848-674     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 261.8mm    |
| 20848-676     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 261.8mm    |
| 20848-677     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 261.8mm    |
| 20848-678     | Anodized     | Etched      | No            | UL® 94V-0           | EN 45545-2, R22-R24, HL3, IEC 60297-3-101 | 261.8mm    |

Table 3/3

| Catalog Number | Width (W) | Quick Ship |
|----------------|-----------|------------|
| 20848-663      | 14.9mm    | No         |
| 20848-664      | 20mm      | No         |
| 20848-665      | 25mm      | No         |
| 20848-666      | 30.1mm    | No         |
| 20848-667      | 35.2mm    | No         |
| 20848-668      | 40.3mm    | No         |
| 20848-669      | 50.5mm    | No         |
| 20848-671      | 14.9mm    | No         |
| 20848-670      | 60.6mm    | No         |
| 20848-672      | 20mm      | No         |



### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**