

# PEMSA Wire Basket Tray C Bracket

## Data Solutions



### CERTIFICATIONS



### FEATURES

Easy to use, quick connect feature

Ideal for ceiling, wall and channel installations

Side load access for cable installation

IEC 61537 load rating and earthing compliant

### SPECIFICATIONS

**Finish:** Electrogalvanized

**Material:** Steel

Table 1/1

| Catalog Number | Article Number | Length 1 (L1) | Length 2 (L2) | Width (W) | Height (H) | Static Load |
|----------------|----------------|---------------|---------------|-----------|------------|-------------|
| WBT100CBRKT    | 820310         | 137mm         | 165mm         | 54mm      | 190mm      | 327N        |

| CatalogNumber | Article Number | Length 1 (L1) | Length 2 (L2) | Width (W) | Height (H) | Static Load |
|---------------|----------------|---------------|---------------|-----------|------------|-------------|
| WBT150CBRKT   | 820320         | 137mm         | 200mm         | 54mm      | 190mm      | 353N        |
| WBT200CBRKT   | 820330         | 137mm         | 265mm         | 54mm      | 190mm      | 284N        |
| WBT300CBRKT   | 820340         | 137mm         | 365mm         | 54mm      | 190mm      | 245N        |
| WBT400CBRKT   | 820350         | 137mm         | 465mm         | 54mm      | 190mm      | 177N        |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE