nVent | ERICO

We connect and protect

Drill Distance Gauge, Three Plates

FEATURES

Used for making precise drill hole spacings of ± 1 mm (0.039")

Common applications include fishplates and insulated rail joints

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Drill Guide Included	Rail Type	Length 1 (L1)	Width (W)
DDG630127	715264	Steel	No	BS113A, 56E1	530.1 mm	87.9 mm

Table 2/2

Catalog Number	Article Number	Height 1 (H1)	A	B
DDG630127	715264	50mm	203 mm	127 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

Our powerful portfolio of brands:
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.