

# Ground Rod Driving Head for Internally Threaded Ground Rods



## FEATURES

Used in conjunction with threaded couplers while driving threaded ground rods


## SPECIFICATIONS

**Material:** Steel

Table 1/1

Catalog Number	Article Number	Ground Rod Diameter, Nominal	Thread Size (TS)	Length (L)	Thread Length (TL)
CDS15	710090	3/8"	M10	38mm	20mm
CDS20	710100	3/8"	M10	41mm	20mm

## DIAGRAMS



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**