

## Side Plinths Stainless Steel, PSS



These plinth side panels close off the extra space underneath the enclosure if needed.

### FEATURES

---

Description: Side panels to cover the openings in the sides of the PFS plinth. Double folded panels for maximum strength. Compatible with combinable and compact stainless steel floor standing ranges.

Material: AISI 304 / AISI 316L pre-grained stainless steel. Panels: 1.5 mm.

Finish: 400 pre-grained stainless steel.

Pack quantity: 2 panels. Mounting accessories included with PFS.

## SPECIFICATIONS

| Table 1/1      |        |       |       |                                |                |                        |
|----------------|--------|-------|-------|--------------------------------|----------------|------------------------|
| Catalog Number | Height | Width | Depth | Enclosure Material             | Product Family | Material               |
| PSS1040        | 100mm  | 400mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>304 |
| PSS2040        | 200mm  | 400mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>304 |
| PSS1050        | 100mm  | 500mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>304 |
| PSS2050        | 200mm  | 500mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>304 |
| PSS1060        | 100mm  | 600mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>304 |
| PSS2060        | 200mm  | 600mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>304 |
| PSS1040-316    | 100mm  | 400mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>316 |
| PSS1050-316    | 100mm  | 500mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>316 |
| PSS1060-316    | 100mm  | 600mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>316 |
| PSS2040-316    | 200mm  | 400mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>316 |
| PSS2050-316    | 200mm  | 500mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>316 |
| PSS2060-316    | 200mm  | 600mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>316 |
| PSS1080-316    | 100mm  | 800mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>316 |
| PSS1100-316    | 100mm  | 999mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>316 |
| PSS2080-316    | 200mm  | 800mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>316 |
| PSS2100-316    | 200mm  | 999mm | 27mm  | Mild Steel,<br>Stainless Steel | Free-Standing  | Stainless Steel<br>316 |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**