

Universal Connection Kit for PI Cables



nVent RAYCHEM CS -150-UNI-PI is a universal under-insulation cold applied connection kit for polymer insulated (PI) heating cables, for splicing and connection of PI heating cables to cold leads (max 32A) or 3-core flexible power cableS (max 25A) using screw terminals. Approved for use in hazardous areas.

FEATURES

Simple and fast to install

Different configurations, tailored to each application

Electrical connections made via terminal block, no special tools required

Approved for use in hazardous areas

SPECIFICATIONS

Table 1/2

Catalog Number	Item Name	Connection Type	Voltage Rating	Current Rating	Max Operating Temperature	IP Rating
A45371-000	CS-150-UNI-PI	Cold Applied	750 V max	32 A	180 °C	IP66

Table 2/2

Catalog Number	Item Name	Area Classification
A45371-000	CS-150-UNI-PI	Non-Hazardous, Hazardous

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT