

Monitor, Keyboard, Touchpad, 1 U Drawer



Designed for standard 19" rackmount designed for comfort
robust design for heavy use or harsh environment operation

CERTIFICATIONS



FEATURES

Pull-out 17" TFT color monitor chassis, 1 U (resolution 1280 x 1024; connects to VGA interface)

Keyboard with different language keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 470 ... 740 mm

SPECIFICATIONS

Depth: 470mm

Product Type: Cabinet/Rack Drawer

Table 1/2

Catalog Number	Rack Height	Package Quantity	Color	Color Code	Type	Works With
60118-580	1U	1	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets

CatalogNumber	Rack Height	Package Quantity	Color	Color Code	Type	Works With
60118-582	1U	1	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets
60118-581	1U	1	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets

Table 2/2

Catalog Number	Keyboard Type	Quick Ship
60118-580	QWERTY UK	No
60118-582	AZERTY	No
60118-581	QWERTZ	No

ADDITIONAL PRODUCT DETAILS

Further versions on request. With trackball or numeric pad.

Other Keyboard layouts see user manual.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE