

# Strut Beam Clip



## FEATURES

Beam Clip for clamping the open side of strut to a beam

Suitable for all strut channels

Requires installation in pairs

Structural attachment to beams to support nVent CADDY Eristrut

FM® Specification Tested

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material                        | Finish             | Flange Thickness (FT) | Hole Size (HS) | Length (L) |
|----------------|----------------|---------------------------------|--------------------|-----------------------|----------------|------------|
| ZTA605         | 388080         | Steel                           | Hot-Dip Galvanized | 16 mm Max             | 13 mm          | 49mm       |
| ZT605HD        | 313260         | Steel                           | Hot-Dip Galvanized | 16 mm Max             | 13 mm          | 49mm       |
| ZTA605S6       | 387190         | Stainless Steel 316 (EN 1.4401) |                    | 16 mm Max             | 13 mm          | 49mm       |

Table 2/2


| Catalog Number | Article Number | Thickness (T) | Width (W) | Static Load | Screw Included |
|----------------|----------------|---------------|-----------|-------------|----------------|
| ZTA605         | 388080         | 6 mm          | 40 mm     | 2040N       | No             |

| Catalog Number | Article Number | Thickness (T) | Width (W) | Static Load | Screw Included |
|----------------|----------------|---------------|-----------|-------------|----------------|
| ZT605HD        | 313260         | 6 mm          | 40 mm     | 2040N       | Yes            |
| ZTA605S6       | 387190         | 6 mm          | 40 mm     | 2040N       | No             |

### ADDITIONAL PRODUCT DETAILS

Indicated loads are based on installation with 1/2" (M12) hardware and strut channel type A.

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221  
 Option 1 – Customer Care  
 Option 2 – Technical  
 Support

#### Europe

Netherlands:  
 +31 800-0200135  
 France:  
 +33 800 901 793

#### Europe

Germany:  
 800 1890272  
 Other Countries:  
 +31 13 5835404

#### APAC

Shanghai:  
 + 86 21 2412 1618/19  
 Sydney:  
 +61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

