

Universal Busbar Support, High Ampacity



CERTIFICATIONS



FEATURES

Universal fixing system

Installs quickly and easily

Extremely robust construction

Screws are made from non-magnetic stainless steel

Halogen free insulators

SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	Material	Max Working Voltage, IEC (Ui)	Working Temperature	Complies With	Flammability Rating
UBS2-10T-160	561520	Steel, Glass Fibre Reinforced Polyamide, Stainless Steel 304 (EN 1.4301)	1000, 1500	-40 to 130 °C	IEC® 60439.1, IEC® 61439.1, IEC® 60695-2-11 (Glow Wire Test 960 °C)	UL® 94V-0


Table 2/3

Catalog Number	Article Number	Typical Application Current Rating	Busbars per Phase	Busbar Width	Busbar Thickness	Width (W)
UBS2-10T-160	561520	5700 A	1 - 2	160 mm	10 mm	307 mm

Table 3/3

Catalog Number	Article Number	A
UBS2-10T-160	561520	110 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE