nVent | HOFFMAN

We connect and protect

# Copper Busbars, WO60



Standard tin-plated Cu busbars used together with busbar supports.

## INDUSTRY STANDARDS

UL

CSA

GL

## FEATURES

Description: Tin-plated Cu busbars. The Cu busbar is effectively protected against aggressive media.

Material: Cu-ETP R300 (EN13601), tinned

Length: 2400 mm

Pack quantity: 1 pc.

Approvals: CSA, UL, GL

## SPECIFICATIONS

Table 1/1

| Catalog Number | Height | Width | Depth | Material | Finish | Cross Section |
|---|---|---|---|---|---|---|
| 01618 | 5mm | 12mm | 2400mm | Copper | Tinned | 60mm² |
| 01619 | 5mm | 15mm | 2400mm | Copper | Tinned | 75mm² |
| 01620 | 5mm | 20mm | 2400mm | Copper | Tinned | 100mm² |
| 01621 | 5mm | 25mm | 2400mm | Copper | Tinned | 125mm² |
| 01623 | 10mm | 12mm | 2400mm | Copper | Tinned | 120mm² |
| 01622 | 5mm | 30mm | 2400mm | Copper | Tinned | 150mm² |
| 01624 | 10mm | 20mm | 2400mm | Copper | Tinned | 200mm² |
| 01625 | 10mm | 30mm | 2400mm | Copper | Tinned | 300mm² |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.