

## Friction Slide, L



These profiles should be used to support heavy equipment and to relieve forces from the 19" profile brackets.

### FEATURES

---

Description: To support heavy components which are only fitted to the front. Mounted between two 19" profiles. Version fixed with 2 screws per profile, and version with click-in fixation.

Material: Click-in version 1.5 mm and mounted version 3 mm zinc plated steel.

Pack quantity: 1 pair with fixing material.

## SPECIFICATIONS

**Thickness:** 3mm  
**Material:** Mild Steel  
**Finish:** Plated

Table 1/1

| Catalog Number | Height | Width | Depth | Max Load | Enclosure Material | Quick Ship |
|----------------|--------|-------|-------|----------|--------------------|------------|
| L597           | 43mm   | 597mm | 42mm  | 980N     | Mild Steel         | No         |
| L406           | 43mm   | 406mm | 42mm  | 980N     | Mild Steel         | No         |
| L406C          | 43mm   | 406mm | 42mm  | 490N     | Mild Steel         | No         |
| L470           | 43mm   | 470mm | 42mm  | 980N     | Mild Steel         | No         |
| L470C          | 43mm   | 470mm | 42mm  | 490N     | Mild Steel         | No         |
| L700           | 43mm   | 700mm | 42mm  | 980N     | Mild Steel         | No         |
| L279           | 43mm   | 279mm | 42mm  | 980N     | Mild Steel         | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**