

# Front Panel, Front Anodized, Rear Conductive, Shielded, Side Hinged, 3 U, 84 HP

## Power Utilities

### CATALOG NUMBER

**20848-611**



Front panel with textile EMC gasket, side hinged assembly.

### CERTIFICATIONS



### FEATURES

Front panel with textile EMC gasket

Enables mounting onto the horizontal rails

Suitable for subracks and cases

Hinges can be fitted on left or right

PRODUCT ATTRIBUTES

|                                   |
|-----------------------------------|
| Product Type: Front Panel         |
| Type: Front Panel without Handle  |
| Mounting: Hinged, Side            |
| EMC Shielding: No (Retrofittable) |
| Gasket Type: Textile              |
| Material: Aluminum                |
| Front Finish: Anodized            |
| Rear Finish: Conductive           |
| Treated Edges: No                 |
| Rack Height: 3 U                  |
| Height: 128.4 mm                  |
| Rack Width: 84 HP                 |
| Width: 426.4 mm                   |
| Package Quantity: 1               |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE