

# Varistar CP Steel Door, Plain With Multi-Point Locking, Shortened



IP55 Steel Door with lever handle and up to 4-Point locking (>2000mm).

## FEATURES

Height of connection plate 400 mm

Connection plate can be assembled on top or bottom

Lever handle with push button

Opening angle 180°

Steel door with up to 4-point locking

## SPECIFICATIONS

**Product Type:** Cabinet Door

Table 1/2

| Catalog Number | Rack Height | Height | Width | Protection Rating | Package Quantity | Color |
|----------------|-------------|--------|-------|-------------------|------------------|-------|
| 21630-372      | 38U         | 1800mm | 600mm | IP55              | 1                |       |
| 21630-373      | 38U         | 1800mm | 800mm | IP55              | 1                |       |
| 21630-374      | 42U         | 2000mm | 600mm | IP55              | 1                |       |
| 21630-375      | 42U         | 2000mm | 800mm | IP55              | 1                |       |

| CatalogNumber | Rack Height | Height | Width | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|-------|-------------------|------------------|------------|
| 21630-376     | 47U         | 2200mm | 600mm | IP55              | 1                |            |
| 21630-377     | 47U         | 2200mm | 800mm | IP55              | 1                |            |
| 21630-711     | 38U         | 1800mm | 600mm | IP55              | 1                | Black Grey |
| 21630-712     | 38U         | 1800mm | 800mm | IP55              | 1                | Black Grey |
| 21630-713     | 42U         | 2000mm | 600mm | IP55              | 1                | Black Grey |
| 21630-714     | 42U         | 2000mm | 800mm | IP55              | 1                | Black Grey |
| 21630-715     | 47U         | 2200mm | 600mm | IP55              | 1                | Black Grey |
| 21630-716     | 47U         | 2200mm | 800mm | IP55              | 1                | Black Grey |

Table 2/2

| Catalog Number | Color Code | Finish        | Locking Type    | Material               | Quick Ship |
|----------------|------------|---------------|-----------------|------------------------|------------|
| 21630-372      |            | Powder Coated | 3-Point Locking | Steel, Stainless Steel | No         |
| 21630-373      |            | Powder Coated | 3-Point Locking | Steel, Stainless Steel | No         |
| 21630-374      |            | Powder Coated | 4-Point Locking | Steel, Stainless Steel | No         |
| 21630-375      |            | Powder Coated | 4-Point Locking | Steel, Stainless Steel | No         |
| 21630-376      |            | Powder Coated | 4-Point Locking | Steel, Stainless Steel | No         |
| 21630-377      |            | Powder Coated | 4-Point Locking | Steel, Stainless Steel | No         |
| 21630-711      | RAL 7021   | Powder Coated | 3-Point Locking | Steel                  | No         |
| 21630-712      | RAL 7021   | Powder Coated | 3-Point Locking | Steel                  | No         |
| 21630-713      | RAL 7021   | Powder Coated | 4-Point Locking | Steel                  | No         |

| Catalog Number | Color Code | Finish        | Locking Type    | Material | Quick Ship |
|----------------|------------|---------------|-----------------|----------|------------|
| 21630-714      | RAL 7021   | Powder Coated | 4-Point Locking | Steel    | No         |
| 21630-715      | RAL 7021   | Powder Coated | 4-Point Locking | Steel    | No         |
| 21630-716      | RAL 7021   | Powder Coated | 4-Point Locking | Steel    | No         |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**