We connect and protect

Varistar CP Server Cabinet, RAL 7021, Side-by-Side, 47 U, 2200H, 800W, 1200D

Data Solutions

CATALOG NUMBER

10630-026

Welded steel frame for high static load requirments.
Prepared for 19" integration of IT assets.

FEATURES

- Preconfigured, ready to use cabinet
- Static load-carrying capacity up to 1600 kg, dynamic 1000 kg
- Ingress protection class IP 20
- Installation of different IT equipment possible
- Integrated air panels for front to back cooling
- Can be easily integrated into aisle containment system

PRODUCT ATTRIBUTES

- Rack Height: 47U
- Height: 2200mm
- Cladding Material: Steel
- Width: 800mm
- Cladding Color: Black Grey
- Depth: 1200mm

Type: Side-by-Side

Package Quantity: 1

Dynamic Load: 1000kgf

Cladding Color Code: RAL 7021

Finish: Powder Coated

Frame Material: Steel

Material: Steel

Product Family: Varistar CP

Product Type: Rack

Static Load: 1600kg

Net Weight: 135.37kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.