

# RackChiller Rear Door Control Unit, Passive

## Data Solutions



The Control Unit enriches the passive RackChiller Rear Door. It connects to the 4 built-in air temperature sensors and the motorized coolant valve 23130-607. This enables the cooler to control the coolant air flow based on a chilled (supply) air temperature setpoint. It provides advanced remote monitoring functionality and various setup features.

## CERTIFICATIONS



## FEATURES

Coolant flow control based on chilled (supply) air temperature setpoint. More control features with water control package 21130-608

Precise flow control against setpoint with parametric PID loop

Remote monitoring through built-in Web Server or BMS protocols (Modbus TCP, SNMP v2c)

Optional external display and keypad 21130-599

Languages: English, German, French

Power Supply: 90 - 260 VAC

## SPECIFICATIONS

Table 1/1

| Catalog Number | Color      |
|----------------|------------|
| 23130-594      | Black Grey |

## ADDITIONAL PRODUCT DETAILS

---

For trouble-free operation it is recommended to use the water connection set and the optional accessories.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**