

FSSB Flat Braid in Coil, Stainless Steel



CERTIFICATIONS



FEATURES

High-quality durable stainless steel 316L provides superior abrasion, corrosion, chemical, and UV resistance for outdoor and corrosive applications

Non-magnetic material

Durability of product lengthens cycle time between maintenance

SPECIFICATIONS

Material: Stainless Steel 316L (EN 1.4404)

Table 1/2

Catalog Number	Article Number	Cross Section	Wire Diameter	Length	Thickness	Width
FSSB25-50	557390	50mm ²	0.25mm	25m	3 mm	30 mm
FSSB25-16	557160	16mm ²	0.25mm	25m	1.5 mm	15 mm
FSSB25-25	557170	25mm ²	0.25mm	25m	1.5 mm	23 mm

Table 2/2

Catalog Number	Article Number	Unit Weight
FSSB25-50	557390	0.44 kg
FSSB25-16	557160	0.14 kg
FSSB25-25	557170	0.22 kg

ADDITIONAL PRODUCT DETAILS

Unit weight is per meter (3.28').

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE