

FS66S Plinth Base

Plinth bases install under an enclosure to provide space for cables to enter from below for type FM FS66S.



FEATURES

1 set for each, consisting of:

2X channel supports on left and right

2X plinth covers for front and rear

All necessary mounting hardware is included

SPECIFICATIONS

Table 1/1

Catalog Number	Material	Finish	Thickness	Fits Enclosure Width	Fits Enclosure Depth	Quick Ship
FMPL0604S010S	Stainless Steel 304	Brushed	2mm	600mm	400mm	No
FMPL0604S020S	Stainless Steel 304	Brushed	2mm	600mm	400mm	No
FMPL0604S030S	Stainless Steel 304	Brushed	2mm	600mm	400mm	No
FMPL0605S010S	Stainless Steel 304	Brushed	2mm	600mm	500mm	No
FMPL0605S020S	Stainless Steel 304	Brushed	2mm	600mm	500mm	No
FMPL0605S030S	Stainless Steel 304	Brushed	2mm	600mm	500mm	No
FMPL0606S010S	Stainless Steel 304	Brushed	2mm	600mm	600mm	No
FMPL0606S020S	Stainless Steel 304	Brushed	2mm	600mm	600mm	No
FMPL0606S030S	Stainless Steel 304	Brushed	2mm	600mm	600mm	No
FMPL0806S010S	Stainless Steel 304	Brushed	2mm	800mm	600mm	No
FMPL0806S020S	Stainless Steel 304	Brushed	2mm	800mm	600mm	No
FMPL0806S030S	Stainless Steel 304	Brushed	2mm	800mm	600mm	No
FMPL0808S010S	Stainless Steel 304	Brushed	2mm	800mm	800mm	No
FMPL0808S020S	Stainless Steel 304	Brushed	2mm	800mm	800mm	No
FMPL0808S030S	Stainless Steel 304	Brushed	2mm	800mm	800mm	No
FMPL1005S010S	Stainless Steel 304	Brushed	2mm	1000mm	500mm	No
FMPL1005S020S	Stainless Steel 304	Brushed	2mm	1000mm	500mm	No
FMPL1005S030S	Stainless Steel 304	Brushed	2mm	1000mm	500mm	No

Catalog Number	Material	Finish	Thickness	Fits Enclosure Width	Fits Enclosure Depth	Quick Ship
FMPL1006S010S	Stainless Steel 304	Brushed	2mm	1000mm	600mm	No
FMPL1006S020S	Stainless Steel 304	Brushed	2mm	1000mm	600mm	No
FMPL1006S030S	Stainless Steel 304	Brushed	2mm	1000mm	600mm	No
FMPL1204S010S	Stainless Steel 304	Brushed	2mm	1200mm	400mm	No
FMPL1204S020S	Stainless Steel 304	Brushed	2mm	1200mm	400mm	No
FMPL1204S030S	Stainless Steel 304	Brushed	2mm	1200mm	400mm	No
FMPL1205S010S	Stainless Steel 304	Brushed	2mm	1200mm	500mm	No
FMPL1205S020S	Stainless Steel 304	Brushed	2mm	1200mm	500mm	No
FMPL1205S030S	Stainless Steel 304	Brushed	2mm	1200mm	500mm	No
FMPL1206S010S	Stainless Steel 304	Brushed	2mm	1200mm	600mm	No
FMPL1206S020S	Stainless Steel 304	Brushed	2mm	1200mm	600mm	No
FMPL1206S030S	Stainless Steel 304	Brushed	2mm	1200mm	600mm	No
FMPL1406S010S	Stainless Steel 304	Brushed	2mm	1400mm	600mm	No
FMPL1406S020S	Stainless Steel 304	Brushed	2mm	1400mm	600mm	No
FMPL1406S030S	Stainless Steel 304	Brushed	2mm	1400mm	600mm	No
FMPL1606S010S	Stainless Steel 304	Brushed	2mm	1600mm	600mm	No
FMPL1606S020S	Stainless Steel 304	Brushed	2mm	1600mm	600mm	No
FMPL1606S030S	Stainless Steel 304	Brushed	2mm	1600mm	600mm	No
FMPL1608S010S	Stainless Steel 304	Brushed	2mm	1600mm	800mm	No
FMPL1608S020S	Stainless Steel 304	Brushed	2mm	1600mm	800mm	No

Catalog Number	Material	Finish	Thickness	Fits Enclosure Width	Fits Enclosure Depth	Quick Ship
FMPL1608S030S	Stainless Steel 304	Brushed	2mm	1600mm	800mm	No
FMPL1910S010S	Stainless Steel 304	Brushed	2mm	1900mm	1000mm	No
FMPL1910S020S	Stainless Steel 304	Brushed	2mm	1900mm	1000mm	No
FMPL1910S030S	Stainless Steel 304	Brushed	2mm	1900mm	1000mm	No
FMPL4010S010S	Stainless Steel 304	Brushed	2mm	4000mm	1000mm	No
FMPL4010S020S	Stainless Steel 304	Brushed	2mm	4000mm	1000mm	No
FMPL4010S030S	Stainless Steel 304	Powder Coated	2mm	4000mm	1000mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE