

ProLine G2 Plinth Base



ProLine G2 Plinth Bases install under an enclosure to provide space for cables to enter from below.

FEATURES

Four access panels for cable management options at the base of the enclosure

Sturdy cast aluminum corner supports for superior performance under load

Corner blocks can be installed onto the base of the frame independent of the cover plates, enabling the cover plates to be attached after integration and just prior to shipment

Stackable up to 400mm in height using Plinth Base Stacking Kit (not included)

100 mm or 200 mm options

To maintain a NEMA Type 12 environmental rating, gland plate must also be used in the base of the enclosure

Installation hardware included

SPECIFICATIONS

Thickness: 1.52mm
Color: Jet Black
Finish: Powder Coated
Color Code: RAL 9005

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth | Material | Quick Ship |
|----------------|----------------|--------|--------|-------|------------|------------|
| P2BP2105 | 31113 | 193mm | 999mm | 464mm | Mild Steel | No |
| P2BP2106 | 31115 | 193mm | 999mm | 564mm | Mild Steel | No |
| P2BP2125 | 31118 | 193mm | 1199mm | 464mm | Mild Steel | No |
| P2BP265 | 31135 | 193mm | 599mm | 464mm | Mild Steel | No |
| P2BP285 | 31143 | 193mm | 799mm | 464mm | Mild Steel | No |
| P2BP286 | 31145 | 193mm | 799mm | 564mm | Mild Steel | No |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE