

# Varistar CP Mobile Base/Plinth

## Power Utilities

Mobile base/plinth to make a cabinet mobile.

### FEATURES

Covers, St, 1.5 mm

Load-carrying capacity on casters 400 kg, on adjustable feet 1000 kg

Support, St, 3 mm

Color RAL 7021

Plinth height H = 103 mm, with feet adjustable from 126 to 134 mm

### SPECIFICATIONS

Table 1/2

| Catalog Number | Width  | Depth   | Color      | Color Code | Product Type      | Type                |
|----------------|--------|---------|------------|------------|-------------------|---------------------|
| 21630-655      | 600 mm | 600 mm  | Black Grey | RAL 7021   | Cabinet/Rack Base | Base Plinth, Mobile |
| 21630-656      | 600 mm | 800 mm  | Black Grey | RAL 7021   | Cabinet/Rack Base | Base Plinth, Mobile |
| 21630-657      | 600 mm | 900 mm  | Black Grey | RAL 7021   | Cabinet/Rack Base | Base Plinth, Mobile |
| 21630-658      | 600 mm | 1000 mm | Black Grey | RAL 7021   | Cabinet/Rack Base | Base Plinth, Mobile |
| 21630-661      | 800 mm | 600 mm  |            |            | Cabinet/Rack Base | Base Plinth, Mobile |
| 21630-662      | 800 mm | 800 mm  | Black Grey | RAL 7021   | Cabinet/Rack Base | Base Plinth, Mobile |
| 21630-663      | 800 mm | 900 mm  | Black Grey | RAL 7021   | Cabinet/Rack Base | Base Plinth, Mobile |

| CatalogNumber | Width  | Depth   | Color      | Color Code | Product Type         | Type                   |
|---------------|--------|---------|------------|------------|----------------------|------------------------|
| 21630-664     | 800 mm | 1000 mm | Black Grey | RAL 7021   | Cabinet/Rack<br>Base | Base Plinth,<br>Mobile |

Table 2/2

| Catalog Number | Works With  |
|----------------|-------------|
| 21630-655      | Varistar CP |
| 21630-656      | Varistar CP |
| 21630-657      | Varistar CP |
| 21630-658      | Varistar CP |
| 21630-661      | Varistar CP |
| 21630-662      | Varistar CP |
| 21630-663      | Varistar CP |
| 21630-664      | Varistar CP |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**