

Modular Junction Box



nVent RAYCHEM JBU-100 is a modular junction box used to connect power to up to three nVent RAYCHEM BTV, QTVR, XTVR, HTV or VPL industrial parallel heating cables. Offered in two versions, customized for local installation practices. All kits are also available with a light for power indication.

FEATURES

Simple and fast to install, spacious boxes with front access, captive lid screws and robust spring type terminals for secure fixing

Part of a modular component system, providing maximum flexibility

One range for all nVent RAYCHEM industrial parallel heating cables

Simplified design in hazardous area, integral part of system approval

Cold-applied: core sealing boot with non-curing sealant; no heat gun, no hot work permit needed

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICATIONS

For Ex-Zone Gas:	1, 2
Inlet Quantity:	4
Connection Clamp Quantity:	6
Max Conductor Cross Section:	10 mm ²
For Ex-Zone Dust:	21, 22
Inlet Type:	Cable
Material:	Glass Fiber Reinforced Polymer
Area Classification:	Non-Hazardous; Hazardous
IP Rating:	IP66
Cover Attachment:	Screwed
Mounting:	Wall/Support Bracket Mounted
Halogen Free:	Yes

Table 1/2

Catalog Number	Item Name	Ambient Temperature	Height	Depth	Width	Light Indication Included
113974-000	JBU-100-L-EP	-40 to 40 °C	160 mm	90 mm	160 mm	Yes
243948-000	JBU-100-EP	-55 to 56 °C	160 mm	90 mm	160 mm	No
051976-000	JBU-100-E	-55 to 56 °C	160 mm	90 mm	160 mm	No
069262-000	JBU-100-L-E	-40 to 40 °C	160 mm	90 mm	160 mm	Yes

Table 2/2

Catalog Number	Item Name	Earth Plate Included	Below Insulation
113974-000	JBU-100-L-EP	Yes	No
243948-000	JBU-100-EP	Yes	No
051976-000	JBU-100-E	No	No
069262-000	JBU-100-L-E	No	No

ADDITIONAL PRODUCT DETAILS

Localized versions may exist with limited approvals and different part numbers. Contact your local sales representative.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT