


TT5000-HUV Fuel Sensing Cable for Aboveground Piping, Modular



nVent RAYCHEM TraceTek TT5000-HUV is a hydrocarbon sensing cable for use on aboveground pipe, around pump pads or valves where the cable will be exposed to sunlight and weather during its service life. The cable is designed to be attached to the bottom of horizontal piping, spiraled around vertical pipe, or placed on flat surfaces below or around pumps and valves and other applications where surface level fuel leaks and spills can be anticipated. Installed with an alarm and locating module, the cable ignores water and detects hydrocarbon fuel leaks, triggers an alarm and pinpoints the location.

FEATURES

Advanced technology: radiation crosslinking and conductive polymer technology, mechanically strong and resistant to chemicals

Simple and fast to install

Easy to design: available in fixed modular lengths, or in bulk form for cut-to-length in field, or in custom cut lengths with connectors attached in the factory

Well documented response times: standard nVent RAYCHEM TraceTek TT5000 sensing core

Distinctive appearance: black rope with red stripe, ready for refinery, tank farm and terminal applications

Flexible and rugged: rope outer layer is fabricated with thousands of individual filaments that add strength and UV protection

Reliable during long life: 5 year product warranty available, maintenance free

SPECIFICATIONS

Outer Diameter:	10.2 mm
Max Operating Temperature:	60 °C
Detection:	Fuel
Detection Method:	Raychem Conductive-Polymer Technology
Model:	Sensing Cable

Table 1/1

Catalog Number	Item Name	Length
P000001299	TT5000-HUV-15M-MC	15 m

Catalog Number	Item Name	Length
P000001302	TT5000-HUV-1M-MC	1 m
P000001296	TT5000-HUV-100M-MC	100 m
P000001300	TT5000-HUV-7.5M-MC	7.5 m
P000001298	TT5000-HUV-30M-MC	30 m
P000001301	TT5000-HUV-3M-MC	3 m
P000001297	TT5000-HUV-50M-MC	50 m

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT