

Countersunk Screw



Countersunk screws are used for numerous mounting options in a subrack or desktop case.

CERTIFICATIONS



FEATURES

Countersunk screw

SPECIFICATIONS

Product Type: Screw

Table 1/2							
Catalog Number	Length	Material	Finish	Package Quantity	Thread Size	Height	
24560-182	12mm	Steel	Zinc Plated	4	M5		
24560-158	7.7mm	Steel	Zinc Plated	100	M2.5		
21100-429	8mm	Steel	Nickel Plated	100	M2.5		
21100-507	12mm	Steel	Nickel Plated	100	M2.5		
21100-500	10mm	Steel	Nickel Plated	100	M2.5		

CatalogNumber	Length	Material	Finish	Package Quantity	Thread Size	Height
21100-649	10mm	Steel	Zinc Plated	100	M2.5	
21100-542	8mm	Steel	Nickel Plated	100	M3	
24560-139	5mm	Steel	Zinc Plated	100	M4	
24560-145	14mm	Steel	Zinc Plated	100	M4	
24560-183	12mm	Steel	Zinc Plated	100	M5	
24560-164	8mm	Steel	Nickel Plated	100	M2.5	4.7mm

			Table 2/2			
Catalog Number	Туре	Width	Works With	Thread Type	Torque	Quick Ship
24560-182	Countersunk Screw		Front Panels		2.4N·m	No
24560-158	Countersunk Screw		Front Panels			No
21100-429	Screw		Front Panels			No
21100-507	Screw		Front Panels			No
21100-500	Screw		Front Panels			No
21100-649	Screw		Front Panels			No
21100-542	Screw		Front Panels			No
24560-139	Countersunk Screw		Front Panels		1.3N·m	No
24560-145	Countersunk Screw		Front Panels		2.4N·m	No
24560-183	Countersunk Screw		Front Panels		2.4N·m	No

CatalogNumber	Туре	Width	Works With	Thread Type	Torque	Quick Ship
24560-164	Countersunk Screw	4.7mm	Front Panels	Metric		No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE