

# RatiopacPRO/-Air Tip-up Handle

Tip-up carrying handles.



## CERTIFICATIONS



## FEATURES

Adjustable in 30° increments

Retrofittable without mechanical tooling on case

Static load-carrying capacity 30 kg

The handle enable a user to have a better view to the front side of the case in case of desktop usage

## SPECIFICATIONS

|                        |                              |
|------------------------|------------------------------|
| <b>Material:</b>       | Aluminum; ABS                |
| <b>Works With:</b>     | Cases                        |
| <b>Product Type:</b>   | Handle                       |
| <b>Product Family:</b> | RatiopacPRO; RatiopacPRO AIR |

Table 1/1

| Catalog Number | Rack Width | Package Quantity | Handle Type   | Color  | Finish        | Quick Ship |
|----------------|------------|------------------|---------------|--------|---------------|------------|
| 24571-320      | 42HP       | 1                | Tip-up Handle | Silver | Powder Coated | No         |

| CatalogNumber | Rack Width | Package Quantity | Handle Type   | Color  | Finish        | Quick Ship |
|---------------|------------|------------------|---------------|--------|---------------|------------|
| 24571-322     | 84HP       | 1                | Tip-up Handle | Silver | Powder Coated | No         |
| 24571-321     | 63HP       | 1                | Tip-up Handle | Silver | Powder Coated | No         |

## ADDITIONAL PRODUCT DETAILS

Cannot be used in conjunction with front handles.

Assembly kit is required for tip-up carrying handle, please order separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**