


# VMEbus J1/J2 Backplane



The nVent SCHROFF VMEbus Backplanes have outstanding high-frequency noise suppression and very high MTBF values due to ceramic capacitors and SMD fabrication technology.

## CERTIFICATIONS



## FEATURES

In accordance with ANSI/VITA 1-1994 VME64 standard

Monolithic backplane, 6 U with J1 and J2 plane

Connection or isolation between the digital GND and chassis GND can be changed via screw

Termination active/passive, switchable via jumpers; passive termination preset

Electronic automatic daisy chain (EDC)

Supply voltages provided via power bugs (ring tag M4) or FASTON

## SPECIFICATIONS

Table 1/3

| Catalog Number | Product Type | Number of Slots | Rack Height | Backplane Type          | System Slot | Slot Width |
|----------------|--------------|-----------------|-------------|-------------------------|-------------|------------|
| 23001-063      | Backplane    | 3               | 6U          | VMEbus, J1/J2, with EDC | Slot 1 Left | 4HP        |
| 23001-064      | Backplane    | 4               | 6U          | VMEbus, J1/J2, with EDC | Slot 1 Left | 4HP        |

| CatalogNumber | Product Type | Number ofSlots | Rack Height | BackplaneType           | System Slot | Slot Width |
|---------------|--------------|----------------|-------------|-------------------------|-------------|------------|
| 23001-065     | Backplane    | 5              | 6U          | VMEbus, J1/J2, with EDC | Slot 1 Left | 4HP        |
| 23001-066     | Backplane    | 6              | 6U          | VMEbus, J1/J2, with EDC | Slot 1 Left | 4HP        |
| 23001-067     | Backplane    | 7              | 6U          | VMEbus, J1/J2, with EDC | Slot 1 Left | 4HP        |
| 23001-068     | Backplane    | 8              | 6U          | VMEbus, J1/J2, with EDC | Slot 1 Left | 4HP        |
| 23001-069     | Backplane    | 9              | 6U          | VMEbus, J1/J2, with EDC | Slot 1 Left | 4HP        |
| 23001-070     | Backplane    | 10             | 6U          | VMEbus, J1/J2, with EDC | Slot 1 Left | 4HP        |
| 23001-072     | Backplane    | 12             | 6U          | VMEbus, J1/J2, with EDC | Slot 1 Left | 4HP        |
| 23001-080     | Backplane    | 20             | 6U          | VMEbus, J1/J2, with EDC | Slot 1 Left | 4HP        |
| 23001-081     | Backplane    | 21             | 6U          | VMEbus, J1/J2, with EDC | Slot 1 Left | 4HP        |

| Table 2/3      |                |                              |                                 |         |         |                  |
|----------------|----------------|------------------------------|---------------------------------|---------|---------|------------------|
| Catalog Number | Connector Type | Power Connector Type         | Utility Connector Type          | Height  | Width   | Package Quantity |
| 23001-063      | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | MicroMatch, 8-pin, 5-pin Header | 263.4mm | 59.5mm  | 1                |
| 23001-064      | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | MicroMatch, 8-pin, 5-pin Header | 263.4mm | 79.8mm  | 1                |
| 23001-065      | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | MicroMatch, 8-pin, 5-pin Header | 263.4mm | 100.2mm | 1                |
| 23001-066      | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | MicroMatch, 8-pin, 5-pin Header | 263.4mm | 120.5mm | 1                |
| 23001-067      | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | MicroMatch, 8-pin, 5-pin Header | 263.4mm | 140.8mm | 1                |
| 23001-068      | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | MicroMatch, 8-pin, 5-pin Header | 263.4mm | 161.1mm | 1                |

| CatalogNumber | ConnectorType  | Power ConnectorType          | Utility ConnectorType           | Height  | Width   | Package Quantity |
|---------------|----------------|------------------------------|---------------------------------|---------|---------|------------------|
| 23001-069     | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | SMCQ, 12-pin, 5-pin Header      | 263.4mm | 181.4mm | 1                |
| 23001-070     | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | MicroMatch, 8-pin, 5-pin Header | 263.4mm | 201.8mm | 1                |
| 23001-072     | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | MicroMatch, 8-pin, 5-pin Header | 263.4mm | 242.4mm | 1                |
| 23001-080     | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | SMCQ, 12-pin, 5-pin Header      | 263.4mm | 405mm   | 1                |
| 23001-081     | DIN 41612, C96 | Power Bugs for M4 Cable Lugs | MicroMatch, 8-pin, 5-pin Header | 263.4mm | 425.3mm | 1                |

| Table 3/3      |            |
|----------------|------------|
| Catalog Number | Quick Ship |
| 23001-063      | No         |
| 23001-064      | No         |
| 23001-065      | No         |
| 23001-066      | No         |
| 23001-067      | No         |
| 23001-068      | No         |
| 23001-069      | No         |
| 23001-070      | No         |
| 23001-072      | No         |
| 23001-080      | No         |
| 23001-081      | No         |

ADDITIONAL PRODUCT DETAILS

Other configurations available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE