

# Washer

Washer used for PCB fixing.



## CERTIFICATIONS



## FEATURES

Washer

## SPECIFICATIONS

**Type:** Washer

**Product Type:** Washer

Table 1/2

| Catalog Number | Material    | Finish        | Package Quantity | Accessory Type    | Color | Height |
|----------------|-------------|---------------|------------------|-------------------|-------|--------|
| 21101-121      | Polyamide 6 |               | 100              | Mounting hardware | White | 5mm    |
| 21100-721      | Steel       | Nickel Plated | 100              | Mounting hardware |       |        |
| 21100-016      | ABS         |               | 100              | Mounting hardware |       |        |
| 21101-964      | Polyamide 6 |               | 100              | Mounting hardware |       |        |

| CatalogNumber | Material | Finish | Package Quantity | AccessoryType     | Color | Height |
|---------------|----------|--------|------------------|-------------------|-------|--------|
| 21100-015     | ABS      |        | 50               | Mounting hardware |       |        |

Table 2/2

| Catalog Number | Product Family                                                                                 | Width | Works With                                                       | Torque | Quick Ship |
|----------------|------------------------------------------------------------------------------------------------|-------|------------------------------------------------------------------|--------|------------|
| 21101-121      |                                                                                                | 5mm   | Backplanes                                                       |        | No         |
| 21100-721      |                                                                                                |       | Front Panels,<br>Frame Type Plug-In Unit                         |        | No         |
| 21100-016      | RatiopacPRO,<br>RatiopacPRO AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO |       | Front Panels,<br>Eurorack,<br>Novastar, Varistar,<br>Varistar CP |        | No         |
| 21101-964      |                                                                                                |       | Front Panels,<br>Eurorack,<br>Novastar, Varistar,<br>Varistar CP | 0.3N·m | No         |
| 21100-015      | RatiopacPRO,<br>RatiopacPRO AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO |       | Front Panels,<br>Eurorack,<br>Novastar, Varistar,<br>Varistar CP |        | No         |

## ADDITIONAL PRODUCT DETAILS

Quantity required for IEEE-Plug-in units (3U/6U)

Quantity required for plug-in units type 2 with extraction handle (3U/6U)

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**