

EB-2X130 Earthing and Neutral Busbar



CERTIFICATIONS



FEATURES

Use to connect several earthing conductors

Chamfered holes allow for easy connections

Main terminal clamp available for thicker conductors

Support bracket available for attaching busbar to DIN rail

Nickel plating is corrosion resistant

Rigid bar

Cut to length as needed

Quick and easy installation


RoHS compliant

SPECIFICATIONS

Catalog Number	EB2X130
Article Number	568674
Material	Brass

Catalog Number	EB2X130
Finish	Nickel Plated
Number of Connections	260
Conductor Size, IEC	1.5 - 25 mm ² Stranded
Max Current Rating	200A
Cross Section	225mm ²
Depth (D)	15mm
Height (H)	15 mm
Width (W)	1000 mm
Hole Size (HS)	6.5 mm
Thread Size (TS)	M5
A	7 mm
Torque (TQ)	2 N·m
Unit Weight	1.59 kg
Complies With	IEC® 60998-2-1

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE