

# Power Socket With Integrated Fuse, LPS



Easy to mount power sockets, to be mounted on a DIN rail, for use when external equipment needs to be plugged in.

## INDUSTRY STANDARDS

---

cULus\_UL listed

CE

GOST

## FEATURES

---

Description: DIN rail mounted electrical socket. Pressure clamp connection for easy and quick wiring.

Dimensions: 92 mm x 62 mm x 48 mm.

Connection: 3 pressure clamps for stranded and rigid wire 0.5-2.5 mm<sup>2</sup>. Integrated fuse 6,3A 5x20 mm.

Finish: Light grey.

Material: Plastic UL 94 V-0.

Pack quantity: 1 piece.

SPECIFICATIONS

**Color:** Light Gray  
**Material:** Plastic  
**Color Code:** RAL 7035  
**Finish:** Smooth

| Table 1/1      |        |       |       |             |        |            |
|----------------|--------|-------|-------|-------------|--------|------------|
| Catalog Number | Height | Width | Depth | Socket Type | Weight | Quick Ship |
| LPS10          | 92mm   | 62mm  | 48mm  | SCHUKO      | 120kg  | No         |
| LPS10CH        | 92mm   | 62mm  | 48mm  | Switzerland | 120kg  | No         |
| LPS10FR        | 92mm   | 62mm  | 48mm  | Type F      | 120kg  | No         |
| LPS10UK        | 92mm   | 62mm  | 48mm  | Type G      | 120kg  | No         |
| LPS10USA       | 92mm   | 62mm  | 48mm  | Type A      | 120kg  | No         |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE