

## Rain Hood, ASST



A stainless steel rain hood provides shelter via a sloped roof and protects installed components from accumulated water dripping into the enclosure when the door is opened.

### FEATURES

Description: To be fitted as an outdoor shelter on stainless steel wall mounted enclosures. The roof is slightly sloped and has a drip strip. Machining is required. Dimensions of the enclosure will be increased by H: 60 mm, W: 20 mm and D: 20 mm

Material: AISI 304 / AISI 316L pre-grained stainless steel

Finish: 400 pre-grained stainless steel

Pack quantity: 1 rain hood with mounting material

Additional information: ASST is not compatible with 180° MMHS hinges

## SPECIFICATIONS

**Finish:** Brushed

Table 1/1

| Catalog Number | Height | Width  | Depth | Material             | Enclosure Material | Product Family |
|----------------|--------|--------|-------|----------------------|--------------------|----------------|
| ASST103        | 59mm   | 1000mm | 300mm | Stainless Steel 304  | Mild Steel         | Wall Mounted   |
| ASST103-316    | 59mm   | 1000mm | 300mm | Stainless Steel 316L | Mild Steel         | Wall Mounted   |
| ASST123        | 59mm   | 1200mm | 300mm | Stainless Steel 304  | Mild Steel         | Wall Mounted   |
| ASST123-316    | 59mm   | 1200mm | 300mm | Stainless Steel 316L | Mild Steel         | Wall Mounted   |
| ASST124        | 59mm   | 1200mm | 400mm | Stainless Steel 304  | Mild Steel         | Wall Mounted   |
| ASST124-316    | 59mm   | 1200mm | 400mm | Stainless Steel 316L | Mild Steel         | Wall Mounted   |
| ASST042        | 59mm   | 400mm  | 210mm | Stainless Steel 304  | Mild Steel         | Wall Mounted   |
| ASST042-316    | 59mm   | 400mm  | 210mm | Stainless Steel 316L | Mild Steel         | Wall Mounted   |
| ASST062        | 59mm   | 600mm  | 210mm | Stainless Steel 304  | Mild Steel         | Wall Mounted   |
| ASST062-316    | 59mm   | 600mm  | 210mm | Stainless Steel 316L | Mild Steel         | Wall Mounted   |
| ASST063        | 59mm   | 600mm  | 300mm | Stainless Steel 304  | Mild Steel         | Wall Mounted   |
| ASST063-316    | 59mm   | 600mm  | 300mm | Stainless Steel 316L | Mild Steel         | Wall Mounted   |
| ASST083        | 59mm   | 800mm  | 300mm | Stainless Steel 304  | Mild Steel         | Wall Mounted   |
| ASST083-316    | 59mm   | 800mm  | 300mm | Stainless Steel 316L | Mild Steel         | Wall Mounted   |
| ASST084        | 59mm   | 800mm  | 400mm | Stainless Steel 304  | Mild Steel         | Wall Mounted   |
| ASST084-316    | 59mm   | 800mm  | 400mm | Stainless Steel 316L | Mild Steel         | Wall Mounted   |

## ADDITIONAL PRODUCT DETAILS

---

Not suitable for AFS.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**