


Plug-In Unit Microswitch for IEL, IET Handle With Cable and Plug

CATALOG NUMBER

20817-606



Micro Switch for IEL or IET handle. The micro switch fits also for the Offset versions of the handle.

CERTIFICATIONS



FEATURES

Plastic, PC, UL 94 V-0

Suitable mating connectors not included in scope of delivery

Max. switched current 50 mA

Electr. life \geq 20,000 switching cycles

Mech. life \geq 20,000 switching cycles

Molex connector housing

Molex crimp contact and fixing clip

PRODUCT ATTRIBUTES

Product Type: Switch

Works With: Front Panels

Material: Polycarbonate

Package Quantity: 10

ADDITIONAL PRODUCT DETAILS

Mating connector not included in delivery. Mating connectors from Molex e.g. 53261-0319, 53048-0310, 53047-0310, 53398-0319, 51047-0300.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE