nVent | SCHROFF

We connect and protect

Frame Type Plug-In Unit Rear Panel Fastener, 5 Pairs

CATALOG NUMBER

24812-401



Rear Panel Fastener for frame type plug-in units, kit with fixing screws. To increase the robustness of wider frame type plug-in units.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

- For connection of rear Panel with cover plate
- To increase robustness of wide frame type plug-in units
- Suitable for plug-in unit cover plates, with perforation for guide rails
- For improved EMC contact between rear Panel and cover plate

PRODUCT ATTRIBUTES

- Package Quantity: 10
- Material: Zinc Alloy
- Product Type: Hardware Kit
- Works With: Cassettes

Net Weight: 0.025kg

ADDITIONAL PRODUCT DETAILS

The rear Panel retainer (24812-402) and retention screw (24560-148) are also available as separate items, 100 pieces; see Accessories.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.