

5000 Beam Clamp Kit



FEATURES

C-Channel system

Includes beam clamp and channel

SPECIFICATIONS

Table 1/2


Catalog Number	Article Number	Material	Finish	Length (L)	Channel Type	Rod Size (RS)
5400S4	335060	Stainless Steel 304 (EN 1.4301)		400mm	E5	10
5800HD	335040	Steel	Hot-Dip Galvanized	800mm	E5	10
5600HD	335030	Steel	Hot-Dip Galvanized	600mm	E5	10
5300HD	335000	Steel	Hot-Dip Galvanized	300mm	E5	10
5500HD	335020	Steel	Hot-Dip Galvanized	500mm	E5	10
5400HD	335010	Steel	Hot-Dip Galvanized	400mm	E5	10
5600S4	335080	Stainless Steel 304 (EN 1.4301)		600mm	E5	10

Table 2/2

Catalog Number	Article Number	Flange Thickness (FT)	Torque (TQ)
5400S4	335060	3 - 30 mm	30 N·m
5800HD	335040	3 - 30 mm	30 N·m
5600HD	335030	3 - 30 mm	30 N·m
5300HD	335000	3 - 30 mm	30 N·m
5500HD	335020	3 - 30 mm	30 N·m
5400HD	335010	3 - 30 mm	30 N·m
5600S4	335080	3 - 30 mm	30 N·m

A	Static Load 1 F1	Static Load 2 F2
100 mm	3500 N	850 N
200 mm	1750 N	400 N
300 mm	1100 N	250 N
400 mm	800 N	200 N
500 mm	700 N	175 N
600 mm	500 N	125 N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

