

# Elbow 45-Degree Feed-Through Stainless Steel



Feed-Through Stainless Steel 45-Degree Elbows are for continuous runs with 45-degree turns. Connects to other wireway sections and fittings and protects wires and cables in frequently hosed down, very wet or highly corrosive applications.

## **INDUSTRY STANDARDS**

---

Certified by Canadian Standards Association.

## **FEATURES**

---

Feed-Through Stainless Steel 45-Degree Elbows are for continuous runs with 45-degree turns

Connects to other wireway sections and fittings and protects wires and cables in frequently hosed down, very wet or highly corrosive applications

## SPECIFICATIONS

---

**Finish:** No. 2B  
**Material:** Stainless Steel 304

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
F66WE45SS	15600	Elbow	152mm	152mm	1.59mm	No
F44WE45SS	15460	Elbow	102mm	102mm	1.59mm	No

## ADDITIONAL PRODUCT DETAILS

---

All dimensions are to outside surfaces. Allow .12 in. (3 mm) additional for gasket at joints. Dimension J is from intersection of center lines.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**