nVent | HOFFMAN

We connect and protect

Mounting Angles (19-inch) Brackets, DNB

These quick and easy to mount brackets to fix 19" profiles provide spacing within the front of 800mm consoles, which allows for equipment to be installed either in a factory or in the field.

FEATURES

Description: For mounting 19" profiles in 800 mm wide enclosures.

Material: 3 mm zinc plated steel.

Pack quantity: 4 brackets with mounting accessories.

SPECIFICATIONS

Table 1/1

Catalog Number	Height	Width	Depth	Material	Finish	Thickness
DNB01	74mm	51mm	78mm	Steel	Zinc Plated	3mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.