

WBT Performance Cable Tray Center Support



The nVent CADDY WBT Performance Tray Center Support is a simple and efficient way to support wire basket trays from a single threaded rod. The offset center tube helps ensure the tray is centered and secured, enhancing both structural integrity and improving project efficiency. Designed for light-duty cable support projects, installation is easy—simply hold the Center Support parallel to the tray, then turn perpendicular until you hear the Center Support lock into place.

Compatible with varying nVent CADDY WBT Performance Cable Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its prepunched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

FEATURES

Use as a central support when hanging with threaded rod

Designed to be used with the nVent CADDY WBT Performance Cable Tray Splice Kit

Supported with 3/8 or ½ in threaded rod

SPECIFICATIONS

Material: Steel

Table 1/2						
Catalog Number	Finish	Color	Height	Width	Length	Height 1
WBTCTSPRT12	Electrogalvaniz ed		193.55 mm	41.4 mm	292.176mm	15.75mm
WBTCTSPRT12 WH	Electrogalvaniz ed	White	193.55 mm	41.4 mm	292.176mm	15.75mm
WBTCTSPRT16 WH	Pregalvanized	White	193.55 mm	41.4 mm	392.201mm	15.75mm

CatalogNumber	Finish	Color	Height	Width	Length	Height 1
WBTCTSPRT18	Pregalvanized		193.55 mm	41.4 mm	442.214mm	15.75mm
WBTCTSPRT4	Electrogalvaniz ed		193.55 mm	41.4 mm	105.156mm	15.75mm
WBTCTSPRT4B A	Electrogalvaniz ed	Black	193.55 mm	41.4 mm	105.156mm	15.75mm
WBTCTSPRT4 WH	Electrogalvaniz ed	White	193.55 mm	41.4 mm	105.156mm	15.75mm
WBTCTSPRT6	Electrogalvaniz ed		193.55 mm	41.4 mm	147.777mm	15.75mm
WBTCTSPRT6 WH	Electrogalvaniz ed	White	193.55 mm	41.4 mm	147.777mm	15.75mm
WBTCTSPRT8	Electrogalvaniz ed		193.55 mm	41.4 mm	190.551mm	15.75mm
WBTCTSPRT8 WH	Electrogalvaniz ed	White	193.55 mm	41.4 mm	190.551mm	15.75mm
WBTCTSPRT16 BA	Pregalvanized	Black	193.55 mm	41.4 mm	392.201mm	15.75mm
WBTCTSPRT18 WH	Pregalvanized	White	193.55 mm	41.4 mm	442.214mm	15.75mm
WBTCTSPRT20 BA	Pregalvanized	Black	193.55 mm	41.4 mm	492.227mm	15.75mm
WBTCTSPRT24	Pregalvanized		193.55 mm	41.4 mm	592.252mm	15.75mm
WBTCTSPRT24 BA	Pregalvanized	Black	193.55 mm	41.4 mm	592.252mm	15.75mm
WBTCTSPRT24 WH	Pregalvanized	White	193.55 mm	41.4 mm	592.252mm	15.75mm

Table 2/2					
Catalog Number	Height 2	Hole Size 1	Hole Size 2	Unit Weight	

WBTCTSPRT12	177.8mm	7.137 mm	5.79 mm	1.225 kg
WBTCTSPRT12WH	177.8mm	7.137 mm	5.79 mm	1.225 kg
WBTCTSPRT16WH	177.8mm	7.137 mm	5.79 mm	1.497 kg
WBTCTSPRT18	177.8mm	7.137 mm	5.79 mm	1.542 kg
WBTCTSPRT4	177.8mm	7.137 mm	5.79 mm	0.7 kg
WBTCTSPRT4BA	177.8mm	7.137 mm	5.79 mm	0.7 kg
WBTCTSPRT4WH	177.8mm	7.137 mm	5.79 mm	0.7 kg
WBTCTSPRT6	177.8mm	7.137 mm	5.79 mm	0.816 kg
WBTCTSPRT6WH	177.8mm	7.137 mm	5.79 mm	0.816 kg
WBTCTSPRT8	177.8mm	7.137 mm	5.79 mm	0.907 kg
WBTCTSPRT8WH	177.8mm	7.137 mm	5.79 mm	0.907 kg
WBTCTSPRT16BA	177.8mm	7.137 mm	5.79 mm	1.497 kg
WBTCTSPRT18WH	177.8mm	7.137 mm	5.79 mm	1.542 kg
WBTCTSPRT20BA	177.8mm	7.137 mm	5.79 mm	1.724 kg
WBTCTSPRT24	177.8mm	7.137 mm	5.79 mm	1.996 kg
WBTCTSPRT24BA	177.8mm	7.137 mm	5.79 mm	1.996 kg
WBTCTSPRT24WH	177.8mm	7.137 mm	5.79 mm	1.996 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE



nVent.com/CADDY 4

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.