


WBT Performance Cable Tray, Round Wire



The nVent CADDY WBT Performance Cable Round Wire Tray is a continuous pathway solution to support high-performance cabling systems while providing an ideal foundation for datacom and electrical contractors.

CERTIFICATIONS



FEATURES

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fiber optic

UL Classified as an equipment ground conductor, no field removal of paint required

T-Weld edge wire for cable and installer protection

Mill Certificates are available to document recycled content for possible LEED credits/certification

SPECIFICATIONS

Material: Steel

Table 1/1

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Unit Weight
WBT2X12	Pregalvanized		50 mm	300	3000mm	6.35 kg
WBT2X12BA	Pregalvanized	Black	50 mm	300	3000mm	6.35 kg

CatalogNumber	Finish	Color	Height (H)	Width (W)	Length (L)	Unit Weight
WBT2X12EG	Electrogalvanized		50 mm	300	3000mm	6.35 kg
WBT2X12WH	Pregalvanized	White	50 mm	300	3000mm	6.35 kg
WBT2X16	Pregalvanized		50 mm	400	3000mm	8.165 kg
WBT2X16BA	Pregalvanized	Black	50 mm	400	3000mm	8.165 kg
WBT2X16EG	Electrogalvanized		50 mm	400	3000mm	8.165 kg
WBT2X16WH	Pregalvanized	White	50 mm	400	3000mm	8.165 kg
WBT2X18	Pregalvanized		50 mm	450	3000mm	8.618 kg
WBT2X18BA	Pregalvanized	Black	50 mm	450	3000mm	8.618 kg
WBT2X18EG	Pregalvanized		50 mm	450	3000mm	8.618 kg
WBT2X18WH	Pregalvanized	White	50 mm	450	3000mm	8.618 kg
WBT2X20	Pregalvanized		50 mm	500	3000mm	9.79 kg
WBT2X20BA	Pregalvanized	Black	50 mm	500	3000mm	9.79 kg
WBT2X20EG	Electrogalvanized		50 mm	500	3000mm	9.79 kg
WBT2X24	Pregalvanized		50 mm	600	3000mm	10.886 kg
WBT2X24BA	Pregalvanized	Black	50 mm	600	3000mm	10.886 kg
WBT2X24EG	Pregalvanized		50 mm	600	3000mm	10.886 kg
WBT2X24WH	Pregalvanized	White	50 mm	600	3000mm	10.886 kg
WBT2X4	Pregalvanized		50 mm	100	3000mm	3.629 kg


CatalogNumber	Finish	Color	Height (H)	Width (W)	Length (L)	Unit Weight
WBT2X4BA	Pregalvanized	Black	50 mm	100	3000mm	3.629 kg
WBT2X4EG	Pregalvanized		50 mm	100	3000mm	3.629 kg
WBT2X4WH	Pregalvanized	White	50 mm	100	3000mm	3.629 kg
WBT2X6	Pregalvanized		50 mm	150	3000mm	4.082 kg
WBT2X6BA	Pregalvanized	Black	50 mm	150	3000mm	4.082 kg
WBT2X6EG	Electrogalvanized		50 mm	150	3000mm	4.082 kg
WBT2X6WH	Pregalvanized	White	50 mm	150	3000mm	4.082 kg
WBT2X8	Pregalvanized		50 mm	200	3000mm	4.436 kg
WBT2X8BA	Pregalvanized	Black	50 mm	200	3000mm	4.535 kg
WBT2X8EG	Electrogalvanized		50 mm	200	3000mm	4.535 kg
WBT2X8WH	Pregalvanized	White	50 mm	200	3000mm	4.436 kg
WBT4X12	Pregalvanized		100 mm	300	3000mm	8.165 kg
WBT4X12BA	Pregalvanized	Black	100 mm	300	3000mm	8.165 kg
WBT4X12EG	Electrogalvanized		100 mm	300	3000mm	8.165 kg
WBT4X12WH	Pregalvanized	White	100 mm	300	3000mm	8.165 kg
WBT4X16	Pregalvanized		100 mm	400	3000mm	9.979 kg
WBT4X16BA	Pregalvanized	Black	100 mm	400	3000mm	9.979 kg
WBT4X16EG	Electrogalvanized		100 mm	400	3000mm	9.979 kg

CatalogNumber	Finish	Color	Height (H)	Width (W)	Length (L)	Unit Weight
WBT4X16WH	Pregalvanized	White	100 mm	400	3000mm	9.979 kg
WBT4X18	Pregalvanized		100 mm	450	3000mm	10.433 kg
WBT4X18BA	Pregalvanized	Black	100 mm	450	3000mm	10.433 kg
WBT4X18EG	Electrogalvanized		100 mm	450	3000mm	10.433 kg
WBT4X18WH	Pregalvanized	White	100 mm	450	3000mm	10.433 kg
WBT4X20	Pregalvanized		100 mm	500	3000mm	10.886 kg
WBT4X20BA	Pregalvanized	Black	100 mm	500	3000mm	10.886 kg
WBT4X20EG	Electrogalvanized		100 mm	500	3000mm	10.886 kg
WBT4X24	Pregalvanized		100 mm	600	3000mm	13.154 kg
WBT4X24BA	Pregalvanized	Black	100 mm	600	3000mm	13.154 kg
WBT4X24EG	Electrogalvanized		100 mm	600	3000mm	13.154 kg
WBT4X24WH	Pregalvanized	White	100 mm	600	3000mm	13.154 kg
WBT4X4	Pregalvanized		100 mm	100	3000mm	4.536 kg
WBT4X4BA	Pregalvanized	Black	100 mm	100	3000mm	4.536 kg
WBT4X4EG	Electrogalvanized		100 mm	100	3000mm	4.536 kg
WBT4X4WH	Pregalvanized	White	100 mm	100	3000mm	4.536 kg
WBT4X6	Pregalvanized		100 mm	150	3000mm	4.99 kg
WBT4X6BA	Pregalvanized	Black	100 mm	150	3000mm	4.99 kg

CatalogNumber	Finish	Color	Height (H)	Width (W)	Length (L)	Unit Weight
WBT4X6EG	Electrogalvanized		100 mm	150	3000mm	4.99 kg
WBT4X6WH	Pregalvanized	White	100 mm	150	3000mm	4.99 kg
WBT4X8	Pregalvanized		100 mm	200	3000mm	6.35 kg
WBT4X8BA	Pregalvanized	Black	100 mm	200	3000mm	6.35 kg
WBT4X8EG	Electrogalvanized		100 mm	200	3000mm	6.35 kg
WBT4X8WH	Pregalvanized	White	100 mm	200	3000mm	6.35 kg
WBT6X12	Pregalvanized		150 mm	300	3000mm	9.979 kg
WBT6X12BA	Pregalvanized	Black	150 mm	300	3000mm	9.979 kg
WBT6X12EG	Electrogalvanized		150 mm	300	3000mm	9.979 kg
WBT6X12WH	Pregalvanized	White	150 mm	300	3000mm	9.979 kg
WBT6X16	Pregalvanized		150 mm	400	3000mm	10.886 kg
WBT6X16BA	Pregalvanized	Black	150 mm	400	3000mm	10.886 kg
WBT6X16EG	Electrogalvanized		150 mm	400	3000mm	10.886 kg
WBT6X18	Pregalvanized		150 mm	450	3000mm	11.34 kg
WBT6X18BA	Pregalvanized	Black	150 mm	450	3000mm	11.34 kg
WBT6X18EG	Pregalvanized		150 mm	450	3000mm	11.34 kg
WBT6X18WH	Pregalvanized	White	150 mm	450	3000mm	11.34 kg
WBT6X20	Pregalvanized		150 mm	450	3000mm	13.154 kg

CatalogNumber	Finish	Color	Height (H)	Width (W)	Length (L)	Unit Weight
WBT6X20BA	Pregalvanized	Black	150 mm	500	3000mm	13.154 kg
WBT6X20EG	Electrogalvanized		150 mm	500	3000mm	13.154 kg
WBT6X24	Pregalvanized		150 mm	600	3000mm	14.515 kg
WBT6X24BA	Pregalvanized	Black	150 mm	600	3000mm	14.515 kg
WBT6X24EG	Electrogalvanized		150 mm	600	3000mm	9.979 kg
WBT6X24WH	Pregalvanized	White	150 mm	600	3000mm	14.515 kg
WBT6X8	Pregalvanized		150 mm	200	3000mm	8.165 kg
WBT6X8BA	Pregalvanized	Black	150 mm	200	3000mm	8.165 kg
WBT6X8EG	Electrogalvanized		150 mm	200	3000mm	8.165 kg
WBT6X8WH	Pregalvanized	White	150 mm	200	3000mm	8.165 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

