

Cable T-Connector



CERTIFICATIONS






FEATURES

For positive bolt tension cable clamping

SPECIFICATIONS

Conductor Size, UL: Class 1 - Class 2 (4/0 Max)

Table 1/1						
Catalog Number	Material	Finish	Depth (D)	Height (H)	Width (W)	Unit Weight
LPA510	Aluminum		43.18mm	18.29 mm	63.5 mm	0.08 kg
LPC510L	Copper	Tinned	43.18mm	18.29 mm	63.5 mm	0.24 kg
LPC510	Copper		43.18mm	18.29 mm	63.5 mm	0.24 kg



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY TRACHTE ERICO HOFFMAN ILSCO SCHROFF