

nVent ERICO Ericore Factory Termination



FEATURES

Upper termination provides an insulated connection from terminal to nVent ERICO Ericore to properly transition the lightning strike

SPECIFICATIONS

Table 1/1				
Catalog Number	Length	Length	Termination Location	
ERICORE/TERM/IN/MEDIUM	100m	100 - 250 m	Internal	
ERICORE/TERM/OUT/MEDIU M	100m	100 - 250 m	External	
ERICORE/TERM/IN/LONG		250 - 500 m	Internal	
ERICORE/TERM/OUT/LONG		250 - 500 m	External	
ERICORE/TERM/OUT/XLONG	500m	500 - 1000 m	External	
ERICORE/TERM/IN/XLONG	500m	500 - 1000 m	Internal	
ERICORETERMOUTSHORT			External	

Catalog Number	Length	Length	Termination Location
ERICORE/TERM/IN/SHORT			Internal

ADDITIONAL PRODUCT DETAILS

Termination location can aid in installation. Choose an inner termination location when spool will be delivered to top of structure and conductor pulled to the grounding location.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France: +33 800 901 793 Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 **APAC**

Shanghai: + 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE