

Mounting Plate, MP-NC



The steel mounting plate contributes to speeding up the assembly of the enclosure, since it can be machined easily and equipped with components before being mounted.

FEATURES

Description: Standard mounting plate. It can also be mounted on the side of an enclosure by using MPS kit or slid in from the side with the MTS profile. For heavy loads in vibrating environments use mounting plate reinforcement profile MPR and MPE or MPEF brackets.

Mounting requirements: Use MPA-NC for mounting the MP-NC inside the enclosure. Adjustable in depth with MPD accessory.

Pack quantity: 1 piece.

Maximum load: 6000 N.

Material: 2.5 mm galvanized steel.

SPECIFICATIONS

Table 1/1						
Catalog Number	Height	Width	Depth	Material	Finish	Thickness
MPNCS1804	1694mm	294mm	25mm	Mild Steel	Galvanized	3mm
MPNCS1805	1694mm	394mm	25mm	Mild Steel	Galvanized	3mm
MPNCS1806	1694mm	494mm	25mm	Mild Steel	Galvanized	3mm
MPNCS1808	1694mm	694mm	25mm	Mild Steel	Galvanized	3mm
MPNCS1810	1694mm	894mm	25mm	Mild Steel	Galvanized	3mm
MPNCS1812	1694mm	1094mm	25mm	Mild Steel	Galvanized	3mm
MPNCS2004	1894mm	294mm	25mm	Mild Steel	Galvanized	3mm
MPNCS2005	1894mm	394mm	25mm	Mild Steel	Galvanized	3mm
MPNCS2006	1894mm	494mm	25mm	Mild Steel	Galvanized	3mm
MPNCS2008	1894mm	694mm	25mm	Mild Steel	Galvanized	3mm
MPNCS2010	1894mm	894mm	25mm	Mild Steel	Galvanized	3mm
MPNCS2012	1894mm	1094mm	25mm	Mild Steel	Galvanized	3mm
MPNCS2206	2094mm	494mm	25mm	Mild Steel	Galvanized	3mm
MPNCS2208	2094mm	694mm	25mm	Mild Steel	Galvanized	3mm
MPNCS2210	2094mm	894mm	25mm	Mild Steel	Galvanized	3mm
MPNCS2212	2094mm	1094mm	25mm	Mild Steel	Galvanized	3mm
MPNCS1606	1600mm		25mm	Zinc Plated		2.5mm
MPNCS1608	1600mm		25mm	Zinc Plated		2.5mm
MPNCS1612	1600mm		25mm	Zinc Plated		2.5mm

ADDITIONAL PRODUCT DETAILS

500 mm width mounting plates for side mounting available on request. 1600 mm wide mounting plates are supplied as two 800 mm wide mounting plates along with a MPF filler plate.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE