


V-Series Full-Size Air Conditioner



V-Series Full-Size Air Conditioners are designed to deliver vital cooling to sensitive electronics. They meet a broad range of cooling requirements, including an all metal shroud to stand up to rugged factory conditions. Units have operating temperature ranges from 20°C to 55°C for indoor models and -40°C to 55°C for outdoor models. The coils are coated for filterless operation in most manufacturing environments or an optional aluminum filter can be used. Each unit is rigorously tested to withstand shipping vibration, high temperatures and other operating challenges.

INDUSTRY STANDARDS

IP34 Ambient side, IP56 Enclosure side

FEATURES

Stock models are equipped with mechanical thermostats at enclosure side

Easy to mount and replace mesh filters

Stock models approved by CE, NEMA 4, IP56 protection class

Compact design can minimize enclosure real estate and maximize cooling capacity at the same overall dimensions

Exterior surface mounting standard

When properly installed to enclosure at the same protection level, it can achieve NEMA 4, IP56 rain-protection level

Operating temperature range from -40 C to 55 C

100% functionally tested

Refrigerant: R134a

Power input: terminal block

Controller: mechanical temperature controller

Thermostat location: enclosure side

Factory thermostat setting (F/C): 86/30

SPECIFICATIONS

Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

Catalog Number	Height	Width	Depth	Nominal Voltage	Remote Access Control	Number of Phases
VA143025G050S	1339mm	434mm	300mm	220V	No	1Ph
VA143025G060S	1339mm	434mm	300mm	220V	No	1Ph
VA143025G070S	1339mm	434mm	300mm	220V	No	1Ph
VA144025G050S	1339mm	434mm	300mm	220V	No	1Ph
VA144025G060S	1339mm	434mm	300mm	220V	No	1Ph
VA144025G070S	1339mm	434mm	300mm	220V	No	1Ph
VA143045G410H	1339mm	434mm	300mm	380V	No	3Ph
VA143045G410S	1339mm	434mm	300mm	380V	No	3Ph
VA144045G410H	1339mm	434mm	300mm	380V	No	3Ph
VA144045G410S	1339mm	434mm	300mm	380V	No	3Ph

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE